





- NOTES:
 1. SUBSTRATE: UV FUSED SILICA
 2. ROHS: COMPLIANT

**FOR INFORMATION ONLY:
 DO NOT MANUFACTURE
 PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
SURFACE QUALITY	80-50
CENTER WAVELENGTH (nm)	220
FULL WIDTH HALF MAX (FWHM) (nm)	10±2
MIN TRANSMISSION (%)	15
CLEAR APERTURE	Ø45.00
BEVEL	PROTECTIVE AS NEEDED



THIRD ANGLE PROJECTION		TITLE	220nm, 10nm FWHM, 50mm DIA. FIRST SURFACE UV BANDPASS FILTER
ALL DIMS IN	mm	DWG NO	14914
			SHEET 1 OF 1