

[All Products](#) / [Testing and Detection](#) / [Spectroscopy](#)

Spectralon® White, Grayscale, and Color Diffuse Reflectance Standards



- Suitable for Spectroscopy, Colorimetry, Radiometry, and Machine Vision Applications
- Diffuse Reflectance Independent of Viewing Angle
- Durable, Stable, and Washable
- Serialized Version with NIST Traceable Calibration Certificate and Data Available

Common Specifications

General

Housing Material:	Delrin
--------------------------	--------

Physical & Mechanical Properties

Thickness (inches):	0.55
----------------------------	------

Diameter (inches):	1.5
---------------------------	-----

Reflective Area Diameter (inches):	1.25
---	------

Environmental & Durability Factors

Operating Temperature (°C):	-80 to 350
------------------------------------	------------

Operating Relative Humidity:	5% - 95%
-------------------------------------	----------

Technical Information

Products

Dia. (inches)	Color	NIST Certification	Stock Number	Price	Buy
1.5	White	No	#54-302	€525,00 Volume Pricing	Contact Us
1.5	White	Yes	#13-512	€625,00 Volume Pricing	10 In Stock
1.5	White and Grayscale	No	#56-078	€1.590,00 Volume Pricing	3 In Stock
1.5	White and Grayscale	Yes	#13-513	€1.875,00 Volume Pricing	Contact Us
1.5	Red, Green, Blue, Yellow	No	#56-079	€1.590,00 Volume Pricing	1 In Stock
1.5	Red, Green, Blue, Yellow	Yes	#13-514	€1.875,00 Volume Pricing	3 In Stock
1.5	Cyan, Orange, Purple, Violet	No	#56-080	€1.510,00 Volume Pricing	2 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com