

[All Products](#) / [Microscopy](#) / [Finite Conjugate Objectives](#)

Mitutoyo Telecentric Objectives See More by [Mitutoyo](#)



- Long Working Distances Allow for Integration into Machine Vision Measurement Systems
- Compact Design and Long Parfocal Length Simplifies Mounting
- [Tube](#) Available for Use with C-Mount Cameras
- Aluminum Alloy Housing

Common Specifications

General			
Manufacturer:		Mitutoyo	Note: Image is formed 280mm from specimen (170mm from the mounting flange)
Optical Properties			
Wavelength Range (nm):		435 - 655	Parfocal Length (mm): 110
Immersion Liquid:		N/A	Maximum Image Circle (mm): 11.00
Sensor			
Maximum Sensor Format:		2/3"	
Threading & Mounting			
Mount:		M26 x 36 TPI	
Mounting Threads:		M26 x 36 TPI	
Environmental & Durability Factors			
Operating Temperature (°C):		+5 to +40	
Operating Humidity:		20 - 80%	

Technical Information

Products

FL (mm)	Magnification	NA	Type	WD (mm)	Stock Number	Price	Buy
175.08	1X	0.03	Microscope Objective	61	#56-984	€2.777,20	2 In Stock
58.51	3X	0.09	Microscope Objective	77	#56-985	€1.505,20	Contact Us
34.74	5X	0.13	Microscope Objective	61	#56-986	€1.282,60	2 In Stock
17.50	10X	0.21	Microscope Objective	51	#56-987	€1.558,20	Contact Us
9.21	20X	0.42	Microscope Objective	20	#87-228	€3.360,20	1 In Stock
3.61	50X	0.55	Microscope Objective	13	#87-229	€4.515,60	Contact Us
1.79	100X	0.70	Microscope Objective	6	#87-230	€6.010,20	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com