


[All Products](#) / [Optics](#) / [Polarization Optics](#) / [Linear Polarizers](#) / [Absorptive \(Dichroic\) Polarizers](#) / [Polymer Film Polarizers](#)

Near-Infrared (NIR) Linear Polarizing Film



- Ideal for NIR Polarization Applications
- >400:1 Extinction Ratio from 800 - 2200nm
- High Efficiency Across Wavelength Range
- Durable Polymer Substrate

Common Specifications



Physical & Mechanical Properties

Construction:	Polarizing Film
---------------	-----------------

Optical Properties

Coating:	Uncoated	Wavelength Range (nm):	400 - 2200
Substrate:	Polymer Film on TAC		

Technical Information



Products

Extinction Ratio	Wavelength Range (nm)	Dia. (mm)	Dimensions (mm)	Dimensional Tolerance (mm)	Thickness (mm)	Stock Number	Price	Buy
#18-938 Clearance								
400:1 (Average @ 800 - 2200nm)	400 - 2200	15.00	-	±0.25	0.50		€55,57	Contact Us
						Clearance		
						Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.		
5,000:1 (400-760nm), 1350:1 (760-2200nm) Average, typical	400 - 2200	10.00	-	+/- 0.25	0.58	#71-116	€50,47 Volume Pricing	2 In Stock
5,000:1 (400-760nm), 1350:1 (760-2200nm) Average, typical	400 - 2200	12.50	-	+/- 0.25	0.58	#71-117	€56,65 Volume Pricing	15 In Stock
5,000:1 (400-760nm), 1350:1 (760-2200nm) Average, typical	400 - 2200	-	12.5 x 12.5	+/- 0.25	0.58	#71-118	€56,65 Volume Pricing	20+ In Stock
5,000:1 (400-760nm), 1350:1 (760-2200nm) Average, typical	400 - 2200	15.00	-	+/- 0.25	0.58	#71-119	€84,46 Volume Pricing	5 In Stock

5,000:1 (400-760nm), 1350:1 (760-2200nm) Average, typical	400 - 2200	20.00	-	+/- 0.25	0.58	#71-120	€108,15 Volume Pricing	20+ In Stock
5,000:1 (400-760nm), 1350:1 (760-2200nm) Average, typical	400 - 2200	25.00	-	+/- 0.25	0.58	#71-121	€144,20 Volume Pricing	Contact Us
5,000:1 (400-760nm), 1350:1 (760-2200nm) Average, typical	400 - 2200	-	25 x 25	+/- 0.25	0.58	#71-122	€144,20 Volume Pricing	20+ In Stock
5,000:1 (400-760nm), 1350:1 (760-2200nm) Average, typical	400 - 2200	30.00	-	+/- 0.25	0.58	#71-123	€204,97 Volume Pricing	13 In Stock
5,000:1 (400-760nm), 1350:1 (760-2200nm) Average, typical	400 - 2200	40.00	-	+/- 0.25	0.58	#71-124	€278,10 Volume Pricing	8 In Stock
5,000:1 (400-760nm), 1350:1 (760-2200nm) Average, typical	400 - 2200	50.00	-	+/- 0.25	0.58	#71-125	€463,50 Volume Pricing	20+ In Stock
5,000:1 (400-760nm), 1350:1 (760-2200nm) Average, typical	400 - 2200	-	50 x 50	+/- 0.25	0.58	#71-126	€463,50 Volume Pricing	13 In Stock
5,000:1 (400-760nm), 1350:1 (760-2200nm) Average, typical	400 - 2200	75.00	-	+/- 0.25	0.58	#71-127	€669,50 Volume Pricing	20+ In Stock

5,000:1 (400- 760nm), 1350:1 (760- 2200nm) Average, typical	400 - 2200	-	76 x 76	+/- 0.25	0.58	#71-128	€669,50 Volume Pricing	15 In Stock
--	------------	---	---------	----------	------	-------------------------	---	-------------



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
 Phone: 1-800-363-1992 :
www.edmundoptics.com