

TECHSPEC[®] 20mm Travel, Adjustable Length Tube



Stock #85-513 2 In Stock

-

1

+

€78²⁸

ADD TO CART

Volume Pricing	
Qty 1+	€78,28 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Function:

Fixed

Physical & Mechanical Properties	
36.5	Overall Length (mm):
10.0 - 30.0	Extension Length (mm):
18.0	Clear Aperture CA (mm):
Black Anodized Aluminum	Construction:
20/25 Dia.	Dimensions (mm):
20.0	Travel (mm):
Threading & Mounting	
M23.2 x 0.75 (Double Male)	Thread Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

PRODUCT DETAILS

- Enable Adjustment of Cage System Length
- Locking Ring for Easy Length Adjustment
- M23.2 x 0.75 Threading
- Combine with [Thread Adapters](#) to Join Multiple Fixed Extension Tubes

M23.2 Adjustable Length Tubes are designed to connect [M23.2 Fixed Extension Tubes](#) or [Cage System Optical Lens Mounts](#) to construct optical assemblies of varying length. One end of the tube is fixed and has M23.2 x 0.75 male threading, while the other end features a locking ring with male M23.2 x 0.75 threading. The locking ring slides along the length of the tube, enabling the adjustment of the system's length.