

[All Products](#) / [Imaging Lenses](#) / [Telecentric Lenses](#)
TECHSPEC® CompactTL™ Telecentric Lenses


- 2/3", C-Mount Telecentric Lens
- Up to 2.3 MegaPixels, 4.5µm Pixel Size Sensors
- Small Telecentric Lens with Coaxial Illumination Options

Common Specifications

General

Series:	CompactTL™ Series	Manufacturer:	Edmund Optics®
----------------	-------------------	----------------------	----------------

Physical & Mechanical Properties

Iris Option:	Fixed
---------------------	-------

Optical Properties

Maximum Image Circle (mm):	11.00
-----------------------------------	-------

Coating:	$\lambda/4$ MgF ₂
-----------------	------------------------------

Sensor



Maximum Sensor Format:	2/3"
-------------------------------	------

Pixel Size (µm):	4.50
-------------------------	------


Threading & Mounting

Mount:	C-Mount
---------------	---------

Technical Information



15.25mm Optical Axis Offset Prism Adapter (Units: mm)



25.25mm Optical Axis Offset Prism Adapter (Units: mm)

Products

Magnification	Max. Sensor Format	FOV @ Max Sensor Format, H x V (mm)	Type of Illumination	WD (mm)	Stock Number	Price	Buy
0.50	2/3"	17.6 x 13.2	-	65	#63-741	€670,00	16 In Stock
0.50	2/3"	17.6 x 13.2	In-Line Illumination	65	#67-310	€1.085,00	20+ In Stock
0.50	2/3"	17.6 x 13.2	-	110	#63-729	€670,00	2 In Stock
0.50	2/3"	17.6 x 13.2	In-Line Illumination	110	#67-303	€1.065,00	16 In Stock
0.75	2/3"	11.7 x 8.8	-	110	#63-730	€670,00	6 In Stock
0.75	2/3"	11.7 x 8.8	In-Line Illumination	110	#67-304	€1.065,00	4 In Stock
0.80	2/3"	11.0 x 8.2	-	65	#63-742	€700,00	10 In Stock
0.80	2/3"	11.0 x 8.2	In-Line Illumination	65	#67-311	€1.110,00	20+ In Stock
1.00	2/3"	8.8 x 6.6	-	40	#63-745	€560,00	10 In Stock
1.00	2/3"	8.8 x 6.6	In-Line Illumination	40	#67-319	€1.000,00	Contact Us
1.00	2/3"	8.8 x 6.6	-	65	#63-733	€560,00	20+ In Stock
1.00	2/3"	8.8 x 6.6	In-Line Illumination	65	#67-312	€1.000,00	20+ In Stock
1.00	2/3"	8.8 x 6.6	-	110	#63-731	€560,00	16 In Stock
1.00	2/3"	8.8 x 6.6	In-Line Illumination	110	#67-305	€990,00	20+ In Stock
1.00	2/3"	8.8 x 6.6	-	220	#33-096	€775,00	10 In Stock

1.00	2/3"	8.8 x 6.6	In-Line Illumination	220	#33-110	€1.170,00	9 In Stock
1.00	2/3"	8.8 x 6.6	-	300	#33-100	€775,00	20+ In Stock
1.00	2/3"	8.8 x 6.6	In-Line Illumination	300	#33-114	€1.170,00	5 In Stock
2.00	2/3"	4.4 x 3.3	-	40	#63-746	€590,00	20+ In Stock
2.00	2/3"	4.4 x 3.3	In-Line Illumination	40	#67-320	€1.020,00	16 In Stock
2.00	2/3"	4.4 x 3.3	-	65	#63-734	€590,00	20+ In Stock
2.00	2/3"	4.4 x 3.3	In-Line Illumination	65	#67-313	€1.020,00	7 In Stock
2.00	2/3"	4.4 x 3.3	-	110	#63-732	€615,00	20+ In Stock
2.00	2/3"	4.4 x 3.3	In-Line Illumination	110	#67-306	€1.045,00	14 In Stock
2.00	2/3"	4.4 x 3.3	-	300	#33-101	€775,00	16 In Stock
2.00	2/3"	4.4 x 3.3	In-Line Illumination	300	#33-115	€1.170,00	14 In Stock
3.00	2/3"	2.9 x 2.2	-	40	#63-747	€615,00	7 In Stock
3.00	2/3"	2.9 x 2.2	In-Line Illumination	40	#67-321	€1.045,00	4 In Stock
3.00	2/3"	2.9 x 2.2	-	65	#63-735	€615,00	5 In Stock
3.00	2/3"	2.9 x 2.2	In-Line Illumination	65	#67-314	€1.045,00	15 In Stock
3.00	2/3"	2.9 x 2.2	-	110	#63-738	€670,00	16 In Stock
3.00	2/3"	2.9 x 2.2	In-Line Illumination	110	#67-307	€1.065,00	4 In Stock
4.00	2/3"	2.2 x 1.6	-	40	#63-748	€635,00	14 In Stock
4.00	2/3"	2.2 x 1.6	In-Line Illumination	40	#67-322	€1.065,00	20+ In Stock

4.00	2/3"	2.2 x 1.6	-	65	#63-736	€635,00	20+ In Stock
4.00	2/3"	2.2 x 1.6	In-Line Illumination	65	#67-315	€1.065,00	20+ In Stock
6.00	2/3"	1.5 x 1.1	-	65	#63-743	€670,00	20+ In Stock
6.00	2/3"	1.5 x 1.1	In-Line Illumination	65	#67-316	€1.085,00	16 In Stock
8.00	2/3"	1.1 x 0.8	-	65	#63-744	€725,00	Contact Us
8.00	2/3"	1.1 x 0.8	In-Line Illumination	65	#67-317	€1.130,00	6 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com