


[All Products](#) /
 [Optics](#) /
 [Polarization Optics](#) /
 [Linear Polarizers](#) /
 [Absorptive \(Dichroic\) Polarizers](#) /
 [Laminated Film Polarizers](#)

Mounted Machine Vision Glass Linear Polarizers



- Up to 3000:1 Extinction Ratio (nominal) @ ~600nm
- Mounted in a Rotating, Locking Housing
- 40-20 Surface Quality

Common Specifications

Physical & Mechanical Properties

Construction:

Black Anodized Aluminum

Optical Properties

Coating:

Hardcoated

Extinction Ratio:

up to 3000:1 @ ~600nm
(nominal)

Surface Quality:

40-20

**Wavelength Range
(nm):**

400 - 700

Technical Information

Products

Filter Thread	Dia. (mm)	Extinction Ratio	CA (mm)	Stock Number	Price	Buy
M105 x 1.00	109.80	up to 3000:1 @ ~600nm	100.00	#21-613	€510,88 Volume Pricing	1 In Stock
M22 x 0.75	23.50	up to 3000:1 @ ~600nm	18.00	#21-528	€106,09 Volume Pricing	2 In Stock
M22.5 x 0.50	24.00	up to 3000:1 @ ~600nm	18.50	#21-545	€73,13 Volume Pricing	1 In Stock
M25.5 x 0.50	27.50	up to 3000:1 @ ~600nm	21.00	#21-749	€73,13 Volume Pricing	1 In Stock
M30.5 x 0.50	32.50	up to 3000:1 @ ~600nm	25.50	#21-766	€78,28 Volume Pricing	5 In Stock
M34 x 0.50	36.00	up to 3000:1 @ ~600nm	29.00	#21-715	€81,37 Volume Pricing	2 In Stock
M35.5 x 0.50	37.50	up to 3000:1 @ ~600nm	30.50	#21-579	€81,37 Volume Pricing	12 In Stock
M37 x 0.75	39.00	up to 3000:1 @ ~600nm	32.50	#21-562	€86,52 Volume Pricing	3 In Stock
M37.5 x 0.50	39.50	up to 3000:1 @ ~600nm	32.50	#21-681	€86,52 Volume Pricing	3 In Stock
M39 x 0.50	41.00	up to 3000:1 @ ~600nm	34.00	#21-426	€86,52 Volume Pricing	1 In Stock
M40.5 x 0.50	42.50	up to 3000:1 @ ~600nm	35.50	#21-664	€86,52 Volume Pricing	5 In Stock
M43 x 0.75	45.00	up to 3000:1 @ ~600nm	38.00	#21-698	€86,52 Volume Pricing	6 In Stock
M46 x 0.75	48.00	up to 3000:1 @ ~600nm	41.00	#21-647	€86,52 Volume Pricing	2 In Stock
M49 x 0.75	51.00	up to 3000:1 @ ~600nm	44.00	#21-443	€86,52 Volume Pricing	2 In Stock
M52 x 0.75	54.00	up to 3000:1 @ ~600nm	47.00	#21-477	€86,52 Volume Pricing	1 In Stock
M55 x 0.75	57.00	up to 3000:1 @ ~600nm	50.00	#21-494	€86,52 Volume Pricing	3 In Stock

M58 x 0.75	60.00	up to 3000:1 @ ~600nm	53.00	#21-732	€86,52 Volume Pricing	6 In Stock
M62 x 0.75	64.00	up to 3000:1 @ ~600nm	57.10	#21-630	€98,88 Volume Pricing	Contact Us
M67 x 0.75	70.00	up to 3000:1 @ ~600nm	62.50	#21-460	€115,36 Volume Pricing	5 In Stock
M72 x 0.75	75.00	up to 3000:1 @ ~600nm	67.50	#21-596	€115,36 Volume Pricing	1 In Stock
M77 x 0.75	80.00	up to 3000:1 @ ~600nm	73.00	#21-409	€131,84 Volume Pricing	5 In Stock
M86 x 1.00	89.00	up to 3000:1 @ ~600nm	81.70	#21-511	€230,72 Volume Pricing	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com