

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#)

IDS Imaging uEye Warp10 10GigE Cameras See More by [IDS Imaging Development Systems](#)





- 10GBASE-T (10GigE) Ethernet Interface, 10X Faster than GigE
- Up to 12.3MP Resolution with Framrates up to 98fps
- Compatible with 1GigE, 2.5GigE and 5GigE Interfaces

Common Specifications

General			
Manufacturer:		IDS Imaging Development Systems	
Camera Series:		uEye+ WP	
Physical & Mechanical Properties			
Dimensions (mm):		60 x 75 x 94.5 (excludes connectors and lens mount)	
Housing:		Full	
Sensor			
Image Buffer:		2032	
Type of Sensor:		Progressive Scan CMOS	
Shutter Type:		Global	
Pixel Depth:		12 bit	
Machine Vision Standard:		GigE Vision	
Hardware & Interface Connectivity			
Interface:		10GigE (PoE)	
Power Supply:		Power over Ethernet (PoE) or via GPIO	
GPIOs:		1 Trigger Input, 1 Flash Output, 2 Fast Output	
Interface Port Orientation:		Back Panel	
GPIO Connector Type:		12-pin M12 connector (Attend 216A-12MSR)	
Threading & Mounting			
Mounting Threads:		¼-20 with Tripod Mount Adapter #16-017	
Environmental & Durability Factors			
Operating Temperature (°C):		0 to +55	
Storage Temperature (°C):		-20 to +60	

Technical Information

Products

Type	Sensor Format	Resolution (Megapixels)	Model Number	Mount	Stock Number	Price	Buy
Monochrome Camera	2"	44.84	GV-77U5WP-M-GL	TFL-Mount	#73-555 New	€7.820,00	Contact Us
					 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
Color Camera	2"	44.84	GV-77U5WP-C-HQ	TFL-Mount	#73-556 New	€7.930,00	Contact Us
					 New Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!		
Color Camera	1.1"	12.30	GV-7000WP-C-HQ	C-Mount	#24-071	€3.455,00	1 In Stock
Monochrome Camera	1.1"	12.30	GV-7000WP-M-GL	C-Mount	#24-072	€3.455,00	Contact Us

Color Camera	2/3"	5.00	GV-7080WP-C-HQ	C-Mount	#24-073	€2.320,00	1 In Stock
Monochrome Camera	2/3"	5.00	GV-7080WP-M-GL	C-Mount	#24-074	€2.320,00	1 In Stock
Color Camera	1"	8.80	GV-7090WP-C-HQ	C-Mount	#24-075	€3.170,00	1 In Stock
Monochrome Camera	1"	8.80	GV-7090WP-M-GL	C-Mount	#24-076	€3.170,00	2 In Stock
Color Camera	1/1.8"	5.10	GV-79F0WP-C-HQ	C-Mount	#28-721	€2.265,00	1 In Stock
Monochrome Camera	1/1.8"	5.10	GV-79F0WP-M-GL	C-Mount	#28-722	€2.265,00	Contact Us
Color Camera	2/3"	8.13	GV-79J0WP-C-HQ	C-Mount	#28-723	€2.490,00	1 In Stock
Monochrome Camera	2/3"	8.13	GV-79J0WP-M-GL	C-Mount	#28-724	€2.490,00	1 In Stock
Color Camera	1/1.1"	12.42	GV-79L0WP-C-HQ	C-Mount	#28-725	€2.840,00	Contact Us
Monochrome Camera	1/1.1"	12.42	GV-79L0WP-M-GL	C-Mount	#28-726	€2.830,00	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com