


[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Plano-Convex \(PCX\) Lenses](#) / [UV and IR Plano-Convex \(PCX\) Lenses](#)

ISP Optics Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses

See More by [ISP Optics](#)



- Low Dispersion and Absorption from 0.6 – 18μm
- High Resistance to Thermal Shock
- Uncoated or BBAR Coated for 8 – 12μm

Common Specifications

Physical & Mechanical Properties

Bevel:	Protective as needed	Centering (arcmin):	<3
---------------	----------------------	----------------------------	----

Optical Properties

Substrate:	Zinc Selenide (ZnSe), CVD Grade	Focal Length Tolerance (%):	±2
Surface Quality:	60-40	Irregularity (P-V) @ 10.6μm:	λ/20

Technical Information

Products

Dia. (mm)	EFL (mm)	BFL (mm)	Coating	Model Number	Stock Number	Price	Buy
#24-947 Clearance							
							
Clearance							
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
25.40	200.00	199.52	Uncoated	ZC-PX-25-200		€357,95	1 In Stock
#24-952 Clearance							
							
Clearance							
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
38.10	75.00	74.14	Uncoated	ZC-PX-38-76		€298,95	6 In Stock

[#24-953 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

38.10 100.00 98.41 Uncoated ZC-PX-38-100

€298,95

3 In Stock

[#24-956 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

38.10 200.00 199.39 Uncoated ZC-PX-38-200

€298,95

5 In Stock

[#24-961 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

50.80 100.00 97.78 Uncoated ZC-PX-50-100

€487,95

3 In Stock

[#24-982 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

12.70 25.40 24.56 BBAR (8000-12000nm) AR812-ZC-PX-12-25

€123,95

14 In Stock

[#24-992 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

25.40	500.00	496.87	BBAR (8000- 12000nm)	AR812- ZC-PX- 25-500	€207,95	1 In Stock
-------	--------	--------	----------------------------	----------------------------	---------	------------

[#24-994 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

38.10	63.50	61.84	BBAR (8000- 12000nm)	AR812- ZC-PX- 38-63	€333,95	3 In Stock
-------	-------	-------	----------------------------	---------------------------	---------	------------

[#24-999 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive
up to 80%
off select
products.

38.10 200.00 199.39 BBAR AR812-
(8000- ZC-PX-
12000nm) 38-200

€333,95

2 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com