


FOCAL LENGTH (EFL):  $48 \pm 0,48$   
 BACK FOCAL LENGTH (BFL):  $47,09$

1 AR COATING: NIR II  
 $R(\text{ABS}) \leq 1,5\%$  FROM 750-800nm @  $0^\circ$  AOI  
 $R(\text{ABS}) \leq 1,0\%$  FROM 800-1550nm @  $0^\circ$  AOI  
 $R(\text{AVG}) \leq 0,7\%$  FROM 750-1550nm @  $0^\circ$  AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$49,14 \pm 0,049$ CX	GLASS N-BK7 517/642	R	$49,14 \pm 0,049$ CX
Øe	11		Øe	11
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION			
ROHS: COMPLIANT	SCALE: NONE $\lambda = 587,6\text{nm}$				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE	12mm Dia, x 48mm FL, NIR II Coated, Double-Convex Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN:	mm	DWG NO
INDICATIONS IN ACCORDANCE WITH ISO 10110				SHEET SIZE	A4
					SHEET 1 OF 1