

NOTES:

1. SUBSTRATE:
N-SF6
2. CENTERING TOLERANCE (AT 587.6nm): <3 ARCMIN
3. COATING (APPLY ACROSS COATING APERTURE)
S1 & S2: V-COAT
R(abs) < 0.25% @ 1550nm @ 0° AOI

4. EDGES: FINE GROUND



5. ASPHERIC FIGURE ERROR: 0.25 μm RMS

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE):



$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS}) * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



COEFFICIENT TABLE 6.	
COEFFICIENT	S1
SEMI-DIAMETER	7.500000E+00
(1/RADIUS)	4.370438E-02
k	-9.730000E-00
D	0.000000E+00
E	3.070373E-06
F	-7.639935E-10
G	0.000000E+00
H	0.000000E+00
J	0.000000E+00
L	0.000000E+00

	S1	S2	EFL@1550nm: 30.00	 Edmund Optics®		
			BFL@587.6nm: 25.65			
SHAPE	CONVEX	PLANO	THIRD ANGLE PROJECTION 	TITLE	15mm Dia., 0.25 NA, V-Coated 1550nm NIR Aspheric Lens	
SURFACE QUALITY	40-20	40-20	ALL DIMS IN	mm	DWG NO	22937
CLEAR APERTURE	Ø 13.5mm	Ø 13.5mm				SHEET 1 OF 1
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				