

NOTES:

1. SUBSTRATE MATERIAL:  
FUSED SILICA

2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN <3 ARCMIN

3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: DIELECTRIC

$R_s(\text{AVG}) \geq 99.90\% @ 800\text{nm} \text{ \& } 1030\text{nm} @ 45^\circ \text{ AOI}$

$R_p(\text{AVG}) \geq 99.90\% @ 800\text{nm} \text{ \& } 1030\text{nm} @ 45^\circ \text{ AOI}$

$R(\text{AVG}) \geq 99.6\% @ 760 - 840\text{nm} @ 45^\circ \text{ AOI}$




$R(\text{AVG}) \geq 99.6\% @ 980 - 1080\text{nm} @ 45^\circ \text{ AOI}$

S2: NONE

4. FINE GRIND SURFACE

5. POWER, IRREGULARITY, SURFACE QUALITY, AND COATING  
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

6. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE FLATNESS	$\lambda/10$	N/A
SURFACE QUALITY	10 - 5	COMMERCIAL POLISH
CLEAR APERTURE	$\phi 11.43$	N/A
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED



ALL DIMS IN

mm



**Edmund Optics®**

TITLE

25.4mm Dia. x 6.35mm 800/1034nm,  
Dual Band Laser Mirror

DWG NO

28966

SHEET  
2 OF 3