

[All Products](#) /
 [Laser Optics](#) /
 [Laser Mirrors](#) /
 [Laser Line Mirrors](#)

Ti:Sapphire Laser Line Mirrors



- >99.8% Reflectivity at Ti:Sapphire Fundamental and Harmonic Frequencies
- 10-5 Surface Quality for Reduced Scatter in Laser Applications
- High Laser Damage Threshold

Common Specifications

Physical & Mechanical Properties

Parallelism (arcmin): <3

Edges: Fine Ground

Optical Properties

Substrate: Fused Silica (Corning 7980)

Surface Flatness (P-V): $\lambda/10$

Surface Quality: 10-5

Technical Information

Products

Wavelength Range (nm)	DWL (nm)	Dia. (mm)	Thickness (mm)	AOI (°)	Stock Number	Price	Buy
390 - 410	400	12.70	6.35	45	#28-983	€134,93	9 In Stock
390 - 410	400	25.40	6.35	45	#28-984	€159,65	20+ In Stock
390 - 410	400	50.80	9.54	45	#28-985	€286,34	5 In Stock
780 - 820	800	12.70	6.35	45	#28-986	€134,93	3 In Stock
780 - 820	800	25.40	6.35	45	#28-987	€159,65	14 In Stock
780 - 820	800	50.80	9.54	45	#28-988	€286,34	2 In Stock
390 - 410	400	12.70	6.35	0-45	#28-989	€146,26	8 In Stock
390 - 410	400	25.40	6.35	0-45	#28-990	€169,95	20+ In Stock
390 - 410	400	50.80	9.54	0-45	#28-991	€297,67	4 In Stock
780 - 820	800	12.70	6.35	0-45	#28-992	€146,26	7 In Stock
780 - 820	800	25.40	6.35	0-45	#28-993	€169,95	20+ In Stock
780 - 820	800	50.80	9.54	0-45	#28-994	€297,67	Contact Us



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Phone: 1-800-363-1992 :
www.edmundoptics.com