



NOTES:

1. SUBSTRATE MATERIAL:  
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: VIS 0° (425-675nm)  
R(AVG) ≤0.4% @ 425 - 675nm



3. FINE GROUND SURFACE

4. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	100.00	 <b>Edmund Optics®</b>
SHAPE	CONVEX	PLANO	BFL	97.98	
RADIUS	51.85	INFINITY			TITLE 25mm H X 50mm L X 100mm FL VIS 0° COATED, CYLINDER LENS
SURFACE QUALITY	60-40	60-40			
CLEAR APERTURE	24.00 x 49.00	24.00 x 49.00	ALL DIMS IN    mm		DWG NO 69734
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED			