



NOTES:

1. SUBSTRATE:  
FLOAT GLASS
2. COATING (APPLY ACROSS CLEAR APERTURE)  
S1: PROTECTED SILVER (450-10,000nm)  
R(AVG) >98% @ 450 - 800nm @ 0° AOI  
R(AVG)>98.5% @ 2000 - 10,000nm @ 0° AOI
- S2: NONE



3. FINE GRIND SURFACE

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                  |                     |                     |  |                                   |        |                 |
|------------------|---------------------|---------------------|--|-----------------------------------|--------|-----------------|
|                  | S1                  | S2                  |  Edmund Optics® |                                   |        |                 |
| SHAPE            | PLANO               | PLANO               |  |                                   |        |                 |
| SURFACE QUALITY  | 60 - 40             | N/A                 |                 | TITLE                             |        |                 |
| SURFACE FLATNESS | 4 - 6λ              | N/A                 |  | 63.5 x 88.9mm Silver, 4-6λ Mirror |        |                 |
| CLEAR APERTURE   | 57.15 x 80.00       | N/A                 |  |                                   |        |                 |
| BEVEL            | PROTECTED AS NEEDED | PROTECTED AS NEEDED | ALL DIMS IN  | mm                                | DWG NO | 71425           |
|                  |                     |                     |  |                                   |        | SHEET<br>7 OF 9 |